

## IE-USB-3.0-A-A-1.8M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Assembled IE cables

### General ordering data

Version	USB cable, USB A 3.0, USB A 3.0, PVC, 1.8 m
Order No.	<a href="#">2581730018</a>
Type	IE-USB-3.0-A-A-1.8M
GTIN (EAN)	4050118650099
Qty.	1 items

**IE-USB-3.0-A-A-1.8M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Length	1.8 m	Length (inches)	70.8661 inch
Net weight	87 g		

**Temperatures**

Storage temperature	Operating temperature	-15 °C...80 °C
Installation temperature		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Technical specifications for cable**

Sheathing colour blue

**General technical data**

Contact surface Gold over nickel

**Cable structure**

Sheathing colour	blue	Cross-section	4*AWG30 + 2*AWG30 + 2*AWG20 (Power)
Sheath diameter, max.	5.65 mm	Sheath diameter, min.	5.35 mm
Material sheath	PVC		

**Plug, left**

Plug left USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded

**Plug, right**

Plug right USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded

**Classifications**

ETIM 8.0	EC001408	ETIM 9.0	EC001408
ETIM 10.0	EC001408	ECLASS 14.0	27-06-01-06
ECLASS 15.0	27-06-01-06		