

## IE-USB-3.0-A-A-5M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Assembled IE cables

### General ordering data

Version	USB cable, USB A 3.0, USB A 3.0, PVC, 5 m
Order No.	<a href="#">2581730050</a>
Type	IE-USB-3.0-A-A-5M
GTIN (EAN)	4050118630558
Qty.	1 items

## IE-USB-3.0-A-A-5M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Length	5 m	Length (inches)	196.8504 inch
Net weight	220 g		

### Temperatures

Storage temperature	Operating temperature	-15 °C...80 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Technical specifications for cable

Sheathing colour	blue
------------------	------

### General technical data

Contact surface	Gold over nickel
-----------------	------------------

### Cable structure

Sheathing colour	blue	Cross-section	4*AWG30 + 2*AWG30 + 2*AWG20 (Power)
Sheath diameter, max.	5.65 mm	Sheath diameter, min.	5.35 mm
Material sheath	PVC		

### Plug, left

Plug left	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded
-----------	--

### Plug, right

Plug right	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded
------------	--

### Classifications

ETIM 8.0	EC001408	ETIM 9.0	EC001408
ETIM 10.0	EC001408	ECLASS 14.0	27-06-01-06
ECLASS 15.0	27-06-01-06		