

IE-USB-3.0-A-A-5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	USB cable, USB A 3.0, USB A 3.0, PVC, 5 m
Order No.	2581730050
Type	IE-USB-3.0-A-A-5M
GTIN (EAN)	4050118630558
Qty.	1 items

IE-USB-3.0-A-A-5M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Length	5 m	Length (inches)	196.8504 inch
Net weight	220 g		

Temperatures

Storage temperature	Operating temperature	-15 °C...80 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical specifications for cable

Sheathing colour	blue
------------------	------

General technical data

Contact surface	Gold over nickel
-----------------	------------------

Cable structure

Sheathing colour	blue	Cross-section	4*AWG30 + 2*AWG30 + 2*AWG20 (Power)
Sheath diameter, max.	5.65 mm	Sheath diameter, min.	5.35 mm
Material sheath	PVC		

Plug, left

Plug left	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded
-----------	--

Plug, right

Plug right	USB A 3.0, IP20, male contact, straight, plug, Plastic, shielded
------------	--

Classifications

ETIM 8.0	EC001408	ETIM 9.0	EC001408
ETIM 10.0	EC001408	ECLASS 14.0	27-06-01-06
ECLASS 15.0	27-06-01-06		