

CABTITE GI I BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The pluggable click inlays allow the frame openings to be configured as required for use with small or large sealing elements. An audible "click" confirms correct installation. This means that the Cabtite cable entry system can be variably configured for different requirements (cables, conductors, hoses, pneumatic and hydraulic lines).

General ordering data

Version	Inlay, Cabtite (cable entry system), Polyamide, glass fibre-reinforced, Deep black, Height: 5 mm, Width: 44 mm, Depth: 17.5 mm, -40 °C...120 °C, IP66
Order No.	2584320000
Type	CABTITE GI I BK
GTIN (EAN)	4050118616071
Qty.	5 items

CABTITE GI I BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223801

Dimensions and weights

Depth	17.5 mm	Depth (inches)	0.689 inch
Height	5 mm	Height (inches)	0.1968 inch
Height of lowest version	17.5 mm	Width	44 mm
Width (inches)	1.7323 inch	Net weight	2.7 g

Temperatures

Operating temperature	-40 °C... 120 °C
-----------------------	------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Silicone	No	UL 94 flammability rating	V-0
Halogen	No	Protection degree	IP66
Basic material	Polyamide, glass fibre-reinforced	Sealing	TPE

Classifications

ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 14.0	27-18-28-15
ECLASS 15.0	27-18-28-15		

CABTITE GI I BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Dimensioned drawing

