

IE-PS-RJ45-TH-BK-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



RJ45 crimp plug-in connector according to IEC
60603-7-51 for wire outer diameters up to 1.05 mm

General ordering data

Version	RJ45 crimp plug, with kink protection; 6.5 - 7.5 mm, Cat.5 (ISO/IEC 11801)
Order No.	2584980000
Type	IE-PS-RJ45-TH-BK-P
GTIN (EAN)	4050118593556
Qty.	10 items

IE-PS-RJ45-TH-BK-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	4.07 g
------------	--------

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
Installation temperature			

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Connection 1	RJ45	Connection 2	Crimp
Description of article	with kink protection; 6.5 - 7.5 mm	Wiring	PROFINET
Colour	Miscellaneous	Insulation cross-section, min.	1.3 mm
Insulation cross-section, max.	1.6 mm	Category	Cat.5 (ISO/IEC 11801)
Contact material	Copper alloy	Connection diameter, solid	0.57...0.64 mm
Conductor connection cross-section, solid (AWG)	AWG 23...AWG 22	Connection diameter, flexible	0.57...0.64 mm
Conductor connection cross-section, flexible (AWG)	AWG 23...AWG 22	Conductor connection cross-section, flexible	...0.35 mm ²
Sheath diameter, max.	7.5 mm	Bending protection sleeve material	Polyamide PA6, UL 94-V0
Shielding	360°; all-round enclosure	Protection degree	IP20
Plugging cycles	750		

Electrical properties



Contact resistance	≤ 10 mΩ	Dielectric strength, contact / shield	≥ 1500 V AC/DC
Dielectric strength, contact / contact	≥ 1000 V AC/DC	Insulation resistance	500 MΩ
Nominal voltage	150 V	Rated current	1.5 A
PoE / PoE+	conforming to IEEE 802.3af		

General standards

Connector standard	IEC 60603-7
--------------------	-------------

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		



IE-PS-RJ45-TH-BK-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

... for modular plug-in connectors



Crimping tools for modular plug-in connector systems WE and DEC

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Three functions in one tool

General ordering data

Type	IE-CWZ-RJ45-TH-P	Version	
Order No.	2614210000	Pressing tool, Crimping tool for contacts	
GTIN (EAN)	4050118621631		
Qty.	1 ST		

Dust caps



For protecting your devices against dust and dirt.

General ordering data

Type	IE-PP-RJ45	Version	
Order No.	2552580000		
GTIN (EAN)	4050118562583		
Qty.	10 ST		