

**THM MULTIMARK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |   |
|------------|---|
| Version    | Marking systems, Thermotransfer printer, Thermal transfer, 300 DPI, MultiMark, Shrink-fit sleeves, Label reel |
| Order No.  | <a href="#">2599430000</a>  |
| Type       | THM MULTIMARK   |
| GTIN (EAN) | 4050118626377   |
| Qty.       | 1 items   |

**THM MULTIMARK**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

|            |        |                 |              |
|------------|--------|-----------------|--------------|
| Depth      | 253 mm | Depth (inches)  | 9.9606 inch  |
| Height     | 320 mm | Height (inches) | 12.5984 inch |
| Width      | 253 mm | Width (inches)  | 9.9606 inch  |
| Net weight | 5800 g |                 |              |

**Temperatures**

Ambient temperature 5 °C...40 °C

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6aI, 6bI, 6c, 7a, 7cI                |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 7d9d08e1-8ede-49b5-a637-5ea27a383bef |

**Labelling systems**

|                                       |   |                        |  |
|---------------------------------------|---|------------------------|--|
| Marker type                           | MultiMark, Shrink-fit sleeves, Label reel   | Memory (RAM)           | 256 MB   |
| System requirements                   | PC with operating system Windows 7, 8 or 10 | Printing method        | Thermal transfer   |
| Interface                             | USB 2.0, Ethernet                           | Software               | M-Print® PRO   |
| Supply voltage                        | 100...240 V AC                              | Operating system       | Windows 7, Windows 8, Windows 8.1, Windows 10, Windows 11  |
| Printing speed                        | max. 150 mm/s                               | Print resolution, max. | 300 DPI  |
| Operation with rechargeable batteries | No  | Included in delivery   | THM MultiMark, Manual, USB cable, Mains cable, Euro plug, US plug, UK plug, Printer driver, RIBBON MM-TB 25/360 SW ink ribbon, RIBBON MM 110/360 SW ink ribbon, Ink ribbon core, Print roller, Pressure roller |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000610    | ETIM 9.0    | EC000610    |
| ETIM 10.0   | EC000610    | ECLASS 14.0 | 24-32-11-90 |
| ECLASS 15.0 | 24-32-11-90 |             |             |