


H0,75/16S W BD GSP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|---|
| Version | Wire-end ferrule, Standard, 12 mm, 10 mm, white |
| Order No. | 2604640000 |
| Type | H0,75/16S W BD GSP |
| GTIN (EAN) | 4050118649444 |
| Qty. | 4200 items |

H0,75/16S W BD GSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E354986 |

Dimensions and weights

| | |
|------------|--------|
| Net weight | 0.15 g |
|------------|--------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | | | |
|------------------------|----------------------------------|---------|----------|
| Description of article | Wire end ferrules on reel, white | Version | Standard |
|------------------------|----------------------------------|---------|----------|

Wire-end ferrules

| | | | |
|-------------------------------|----------------------|---|-------------|
| Contact surface diameter (D1) | 1.2 mm | Contact surface length (L2) | 10 mm |
| Collar diameter (D2) | 3.4 mm | Plastic collar thickness (S2) | 0.25 mm |
| L1 in mm | 16.00 mm | Wire connection cross section AWG, max. | AWG 18 |
| Metal sleeve thickness (S1) | 0.15 mm | Stripping length | 12 mm |
| Conductor cross-section | 0.75 mm ² | Colour code | Weidmueller |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ETIM 10.0 | EC000005 | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 | | |

Drawing

