

## H0,75/16DS GR BD GSP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Version	Wire-end ferrule, Standard, 12 mm, 10 mm, grey
Order No.	<a href="#">2604650000</a>
Type	H0,75/16DS GR BD GSP
GTIN (EAN)	4050118649451
Qty.	4200 items

**H0,75/16DS GR BD GSP**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E354986

**Dimensions and weights**

Net weight	0.12 g
------------	--------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Technical data**

Description of article	Reel of wire end ferrules, grey	Version	Standard
------------------------	---------------------------------	---------	----------

**Wire-end ferrules**

Contact surface diameter (D1)	1.2 mm	Contact surface length (L2)	10 mm
Collar diameter (D2)	3.4 mm	Plastic collar thickness (S2)	0.25 mm
L1 in mm	16.00 mm	Wire connection cross section AWG, max.	AWG 18
Metal sleeve thickness (S1)	0.15 mm	Stripping length	12 mm
Conductor cross-section	0.75 mm <sup>2</sup>	Colour code	DIN

**Classifications**

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

