


## SQB 3/4

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### General ordering data

Version	Cross-connector (terminal), when screwed in, black, 41 A, Number of poles: 4, Pitch in mm (P): 9.00, Insulated: Yes, Width: 32.1 mm
Order No.	<a href="#">2615130000</a>
Type	SQB 3/4
GTIN (EAN)	4050118653854
Qty.	50 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	2.8 mm	Depth (inches)	0.1102 inch
Height	24 mm	Height (inches)	0.9449 inch
Width	32.1 mm	Width (inches)	1.2638 inch
Net weight	2.21 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Wemid, PA	Colour	black
UL 94 flammability rating	V-2		

### System specifications

Version	Cross-connector
---------	-----------------

### Additional technical data

Type of fixing	when screwed in	Explosion-tested version	No
Type of mounting	when screwed in		

### Dimensions

Pitch in mm (P)	9.00 mm
-----------------	---------

### General

Number of poles	4
-----------------	---

### Rating data

Rated voltage	400 V	Nominal current	41 A
---------------	-------	-----------------	------

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		