
Data sheet

SQBA 4/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, black, 41 A, Number of poles: 3, Pitch in mm (P): 22.00, Insulated: Yes, Width: 49.6 mm
Order No.	2615170000
Type	SQBA 4/3
GTIN (EAN)	4050118653816
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Last order date	2027-04-30T00:00:00+02:00

Data sheet

SQBA 4/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	2.5 mm	Depth (inches)	0.0984 inch
Height	27.6 mm	Height (inches)	1.0866 inch
Width	49.6 mm	Width (inches)	1.9528 inch
Net weight	5.02 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid, PA	Colour	black
UL 94 flammability rating	V-2		

System specifications

Version	Cross-connector

Additional technical data

Type of fixing	when screwed in	Explosion-tested version	No
Type of mounting	when screwed in		

Dimensions

Pitch in mm (P)	22.00 mm

General

Number of poles	3

Rating data

Rated voltage	400 V	Nominal current	41 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		