

SAKQB 6/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, Number of poles: 2, Pitch in mm (P): 8.00, Insulated: No, Width: 6 mm
Order No.	2615330000
Type	SAKQB 6/2
GTIN (EAN)	4050118655797
Qty.	20 items
Local product	Only available in certain countries

Technical data

Approvals

ROHS Conform

General ordering data

Local product Only available in certain countries

Dimensions and weights

Depth	15 mm	Depth (inches)	0.5906 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	3.86 g		

Temperatures

Storage temperature -25 °C...55 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Material data

Colour grey

Additional technical data

Type of fixing when screwed in Explosion-tested version No

Dimensions

Pitch in mm (P) 8.00 mm

General

Number of poles 2

Rating data

Rated voltage 400 V

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		