

DEK 5/8 MM BP WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

| | |
|------------|--|
| Version | Dekafix, Terminal marker, 5 x 8 mm, Weidmueller, white |
| Order No. | 2619790000 |
| Type | DEK 5/8 MM BP WS |
| GTIN (EAN) | 4050118626292 |
| Qty. | 6000 items |

DEK 5/8 MM BP WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Height | 5 mm | Height (inches) | 0.1968 inch |
| Width | 8 mm | Width (inches) | 0.315 inch |
| Net weight | 0.11 g | | |

Temperatures

Operating temperature range -50...90 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|-----------------------------------|-------------------------|-----------------------------------|--|
| Orientation of print | horizontal and vertical | Version | halogen-free |
| Width | 8 mm | UL 94 flammability rating | V-2 |
| Operating temperature range, max. | 90 °C | Operating temperature range, min. | -50 °C |
| Colour | white | Halogen | No |
| Basic material | PC-ABS, TPU | Printed characters | without |
| Size of labelling field | 4.5 x 7.5 mm | compatible printer | THM MULTIMARK , THM MULTIMARK PLUS |
| Operating temperature range | -50...90 °C | Application/manufacturer | Weidmueller |

Important note

Product information External roll holder 1302920000 necessary

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000761 | ETIM 9.0 | EC000761 |
| ETIM 10.0 | EC000761 | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 | | |

Drawings

