

EL CC-RAIL MM GE 30M**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Customised identification: EL

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the height can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

Your benefits with MultiMark

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

| | |
|------------|------------------------------------|
| Version | THM, Device markers, 15 x , yellow |
| Order No. | 2619980000 |
| Type | EL CC-RAIL MM GE 30M |
| GTIN (EAN) | 4050118626100 |
| Qty. | 1 items |

EL CC-RAIL MM GE 30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 0.08 mm | Depth (inches) | 0.0031 inch |
| Height | 15 mm | Height (inches) | 0.5906 inch |
| Length | 30000 mm | Length (inches) | 1181.1 inch |
| Net weight | 125 g | | |

Temperatures

Operating temperature range -50...100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|-----------------------------------|--------------------------------------------------------------------|-----------------------------------|---------------|
| Version | halogen-free | UL 94 flammability rating | HB |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -50 °C |
| Colour | yellow | Halogen | No |
| Length | 30000 mm | Basic material | Polypropylene |
| Printed characters | without | Approval acc. to UL 969 | Yes |
| compatible printer | THM MULTIMARK , THM MULTIMARK PLUS | Operating temperature range | -50...100 °C |
| Number per roll | 1 | | |

Device markers

Halogen No

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings



EL CC-RAIL MM GE 30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|------------|--|
| Type | RIBBON MM 76/360 SW | Version | |
| Order No. | 2005080000 | Ink ribbon | |
| GTIN (EAN) | 4050118389951 | | |
| Qty. | 1 ST | | |

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | THM MMP EXT.RH | Version | |
| Order No. | 1302920000 | | |
| GTIN (EAN) | 4050118102307 | | |
| Qty. | 1 ST | | |
| Type | MULTIMARK ROLLER 115 | Version | |
| Order No. | 1357420000 | | |
| GTIN (EAN) | 4050118160314 | | |
| Qty. | 1 ST | | |

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

EL CC-RAIL MM GE 30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

General ordering data

| | | |
|------------|----------------------------|---------|
| Type | MULTIMARK PLUS ROLLER 1... | Version |
| Order No. | 2672590000 | |
| GTIN (EAN) | 4050118708097 | |
| Qty. | 1 ST | |