

## ESG-FO 6/17 MM WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Guaranteed long service life: ESG

The multi-colour and multi-format labels have a strong adhesive layer to ensure the best possible adhesion to the underlying surface. Double laminated polyester makes the basic material very thin and yet extremely tear-resistant.

### Your benefits with MultiMark

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

### General ordering data

|            |                                       |
|------------|---------------------------------------|
| Version    | ESG, Device markers, 6 x 17 mm, white |
| Order No.  | <a href="#">2619990000</a>            |
| Type       | ESG-FO 6/17 MM WS                     |
| GTIN (EAN) | 4050118626094                         |
| Qty.       | 1000 items                            |

**ESG-FO 6/17 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.55 mm | Depth (inches)  | 0.0217 inch |
| Height     | 6 mm    | Height (inches) | 0.2362 inch |
| Width      | 17 mm   | Width (inches)  | 0.6693 inch |
| Net weight | 0.06 g  |                 |             |

**Temperatures**

Operating temperature range -30...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

|                                   |                                                                    |                                   |                             |
|-----------------------------------|--------------------------------------------------------------------|-----------------------------------|-----------------------------|
| Adhesive                          | PE-foam with acrylic adhesive                                      | Version                           | Self-adhesive, halogen-free |
| Width                             | 17 mm                                                              | UL 94 flammability rating         | V-0                         |
| Operating temperature range, max. | 80 °C                                                              | Operating temperature range, min. | -30 °C                      |
| Colour                            | white                                                              | Halogen                           | No                          |
| Basic material                    | Polyester                                                          | Printed characters                | without                     |
| Size of labelling field           | 6 x 17 mm                                                          | Approval acc. to UL 969           | Yes                         |
| compatible printer                | <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a> | Operating temperature range       | -30...80 °C                 |

**Device markers**

Halogen No

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |

**Drawings**



## ESG-FO 6/17 MM WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

|            |                            |            |  |
|------------|----------------------------|------------|--|
| Type       | RIBBON MM 76/360 SW        | Version    |  |
| Order No.  | <a href="#">2005080000</a> | Ink ribbon |  |
| GTIN (EAN) | 4050118389951              |            |  |
| Qty.       | 1 ST                       |            |  |

### THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

|            |                            |         |  |
|------------|----------------------------|---------|--|
| Type       | MULTIMARK ROLLER 115       | Version |  |
| Order No.  | <a href="#">1357420000</a> |         |  |
| GTIN (EAN) | 4050118160314              |         |  |
| Qty.       | 1 ST                       |         |  |

### THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

|            |                            |         |  |
|------------|----------------------------|---------|--|
| Type       | MULTIMARK PLUS ROLLER 1... | Version |  |
| Order No.  | <a href="#">2672590000</a> |         |  |
| GTIN (EAN) | 4050118708097              |         |  |
| Qty.       | 1 ST                       |         |  |