

## CC-FO 15/45 MM WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Standard included: CC

Our systematically matching product range includes labels for identifying standardised components, as well as all-purpose and familiar formats such as the CC 85/54 marker for nameplates.

Your benefits with MultiMark

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

### General ordering data

|            |   |
|------------|---|
| Version    | ClipCard, Device markers, 15 x 45 mm, white |
| Order No.  | <a href="#">2621340000</a>                  |
| Type       | CC-FO 15/45 MM WS                           |
| GTIN (EAN) | 4050118625707                               |
| Qty.       | 500 items                                   |

## CC-FO 15/45 MM WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.55 mm | Depth (inches)  | 0.0217 inch |
| Height     | 15 mm   | Height (inches) | 0.5906 inch |
| Width      | 45 mm   | Width (inches)  | 1.7716 inch |
| Net weight | 0.3 g   |                 |             |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|                                   |  |                                   |                             |
|-----------------------------------|--|-----------------------------------|-----------------------------|
| Adhesive                          | PE-foam with acrylic adhesive                                      | Version                           | Self-adhesive, halogen-free |
| Width                             | 45 mm  | UL 94 flammability rating         | V-0                         |
| Operating temperature range, max. | 80 °C  | Operating temperature range, min. | -30 °C                      |
| Colour                            | white  | Halogen                           | No                          |
| Basic material                    | Polyester  | Printed characters                | without                     |
| Size of labelling field           | 15 x 44.5 mm   | Approval acc. to UL 969           | Yes                         |
| compatible printer                | <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a> | Operating temperature range       | -30...80 °C                 |
| Number per roll                   | 500  |                                   |                             |

### Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |

**Drawings**

