


HS-FR 19.1-38.1/50 MM Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 19.1 - 38.1 mm, 49.8 x 60.8 mm, yellow
Order No.	2621910000
Type	HS-FR 19.1-38.1/50 MM Y
GTIN (EAN)	4050118625134
Qty.	100 items
Delivery status	This article will no longer be available in the future.
Available until	2025-08-31T00:00:00+02:00
Alternative product	HS-HF 19.5-38.1/50 MM Y

HS-FR 19.1-38.1/50 MM Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.77 mm	Depth (inches)	0.0303 inch
Height	49.8 mm	Height (inches)	1.9606 inch
Width	60.8 mm	Width (inches)	2.3937 inch
Net weight	3.8 g		

Temperatures

Operating temperature range	-55...125 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	60.8 mm
Operating temperature range, max.	125 °C	Operating temperature range, min.	-55 °C
Colour	yellow	Halogen	No
Basic material	Polyolefine	Printed characters	without
Size of labelling field	60.8 x 49.8 mm	compatible printer	THM MULTIMARK , THM MULTIMARK PLUS
Operating temperature range	-55...125 °C	Number per roll	100

Conductor and cable markers

Wire connection cross section AWG, max.	AWG 450 MCM	Halogen	No
Wire connection cross section AWG, min.	AWG 2/0	Conductor cross-section, max.	240 mm ²
Conductor cross-section, min.	70 mm ²	Conductor O.D., max.	38.1 mm
Conductor O.D., min.	19.1 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	19.1 - 38.1 mm
Cross-section for connected wire	70 - 240 mm ²		

Classifications


ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

HS-FR 19.1-38.1/50 MM Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HS-FR 19.1-38.1/50 MM Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM-HS 60/300 SW	Version	
Order No.	2448880000	Ink ribbon	
GTIN (EAN)	4050118462944		
Qty.	1 ST		

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK ROLLER 115	Version	
Order No.	1357420000		
GTIN (EAN)	4050118160314		
Qty.	1 ST		

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	MULTIMARK PLUS ROLLER 1...	Version	
Order No.	2672590000		
GTIN (EAN)	4050118708097		
Qty.	1 ST		