

THM WO VIN 25.4/36.5 GE IW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 4 - 7.5 mm, 25.4 x 36.5 mm, yellow
Order No.	2625560000
Type	THM WO VIN 25.4/36.5 GE IW
GTIN (EAN)	4050118628968
Qty.	2500 items

THM WO VIN 25.4/36.5 GE IW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.07 mm	Depth (inches)	0.0026 inch
Height	25.4 mm	Height (inches)	1 inch
Width	36.5 mm	Width (inches)	1.437 inch
Net weight	0.2 g		

Temperatures

Operating temperature range -40...150 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive		
Type of printing	neutral		
Width	36.5 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Colour	yellow		
Number of markers per packaging unit	Form of supply	Label reel	
Size of labelling field	12.7 x 25.4 mm		
compatible printer			
Number of markers per combination	1 Label reel = Conductor and cable markers		
Operating temperature range	-40...150 °C		
Number per roll	2500		

Conductor and cable markers

Conductor O.D., max.	7.5 mm	Conductor O.D., min.	4 mm
Conductor O.D.	4 - 7.5 mm		

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		