


VT-TM 5/18 HF-V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	, Socket x 5.3 mm, Polyester, TPU, Colour: yellow, Transparent, Conductor O.D.: 24 - 35 mm
Order No.	2633080000
Type	VT-TM 5/18 HF-V0
GTIN (EAN)	4050118695144
Qty.	50 items

VT-TM 5/18 HF-V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	37.19 mm	Depth (inches)	1.4642 inch
Height	18 mm	Height (inches)	0.7087 inch
Width	5.3 mm	Width (inches)	0.2087 inch
Net weight	1.55 g		

Temperatures

Operating temperature range -30...90 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	5.3 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	90 °C
Operating temperature range, min.	-30 °C	Colour	yellow, Transparent
Halogen	No	Basic material	Polyester, TPU
Printed characters	without	Recommended industries	Transportation, Machinery
Operating temperature range	-30...90 °C		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	70 mm ²
Conductor cross-section, min.	25 mm ²	Conductor O.D., max.	35 mm
Conductor O.D., min.	24 mm	Conductor O.D.	24 - 35 mm
Cross-section for connected wire	25 - 70 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		