

FP ENC DR07 142 XB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Extensive range of accessories for the FieldPower® boxes.
Cable seals, terminal rails, locking elements and much more.

General ordering data

Version	Field Power® terminal rail, Steel, galvanized, 142 mm, for base part
Order No.	2633450000
Type	FP ENC DR07 142 XB
GTIN (EAN)	4050118664416
Qty.	5 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	35 mm	Height (inches)	1.378 inch
Width	142 mm	Width (inches)	5.5905 inch
Net weight	10.8 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...85 °C
---------------------	-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General specifications

Insulating material	Steel	Basic material	Steel, galvanized
Colour	silver, black		

General data

Basic material	Steel, galvanized	Insulating material	Steel
Colour	silver, black	Type of mounting	Plugged
Mounting position, installation notice	for base part	Version	without slot

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

Drawings

