

WPC WAGON**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Optional accessories to customise the Wire Processing Center. Cable feeding system directly on the workshop trolley or on an external unit, additional printers or gripper trays.

General ordering data

Version	Automatic machines
Order No.	2634140000
Type	WPC WAGON
GTIN (EAN)	4050118688122
Qty.	1 items

WPC WAGON

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	750 mm	Depth (inches)	29.5275 inch
Height	1800 mm	Height (inches)	70.866 inch
Width	1100 mm	Width (inches)	43.307 inch
Net weight	30000 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5.5 bar	Electrical connection	100 - 240 V AC / 50/60 Hz
---------------------------	---------	-----------------------	---------------------------

Automatic cutting

Compressed-air connection	5.5 bar	Electrical connection	100 - 240 V AC / 50/60 Hz
---------------------------	---------	-----------------------	---------------------------

WPC

Electrical connection	100 - 240 V AC / 50/60 Hz	Type of display	15-inch touchscreen
Note	pivoting display holder, Load capacity max. 180 kg. Panel with completed cabling and additional mains plugs and USB connections, Mobile use	Compressed-air connection	5.5 bar

Classifications

ETIM 8.0	EC011808	ETIM 9.0	EC011808
ETIM 10.0	EC011808	ECLASS 14.0	21-07-03-08
ECLASS 15.0	21-07-03-08		