

## HDC XX6A02 FFSXXXX-0500

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Compact

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

### General ordering data

Order No.	2634700500
Type	<a href="#">HDC XX6A02 FFSXXXX-0500</a>
GTIN (EAN)	4050118650143
Qty.	1 items

**HDC XX6A02 FFSXXX-0500**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 1 g

**Temperatures**

Limit temperature -30 °C ... 90 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant with exemption  
 RoHS Exemption (if applicable/known) 6c  
 REACH SVHC Lead 7439-92-1  
 SCIP 2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5

**General data**

Number of poles	8	Cable length	5 m
Coding	X-coded	Contact surface	Au (Gold)
Transmission rate	10 Gbps, 10 Gbit/s	Insulation resistance	≥ 108 Ω
Category	Cat. 6A	Nominal voltage	50 V
Nominal current	0.5 A	Plugging cycles	≥ 100
Pollution severity	2	Opposite side version	Female, straight
Module side version	Female		

**Cable technical specifications**

Cable length	5 m	Sheathing colour	green
Halogen	halogen-free, according to IEC 60754-1	Sheath material	PUR

**Classifications**

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-07
ECLASS 15.0	27-06-03-07		