

**HDC MPN 2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

**General ordering data**

Version	Pneumatic module, Number of poles: 2, Hose connection (pneumatic), pneumatic, Required plug-in slots: 1
Order No.	<a href="#">2637320000</a>
Type	HDC MPN 2
GTIN (EAN)	4050118767520
Qty.	1 items

## HDC MPN 2

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Net weight	6.26 g
------------	--------

### Temperatures

Limit temperature	-40 °C ... 80 °C
-------------------	------------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

### General data

Number of poles	2	UL 94 flammability rating	V-0
Plugging cycles	≥ 500	Type	pneumatic
Basic material	Polycarbonate, glass fibre reinforced	Series	ModuPlug
Required plug-in slots	1		

### Pneumatic module

Module operating pressure	8 bar	Inner hose diameter, min.	6 mm
Inner hose diameter, max.	6 mm		

### Version

Type of connection	Hose connection (pneumatic)	Conductor cross-section, max.	0 mm <sup>2</sup>
Conductor cross-section, min.	0 mm <sup>2</sup>		

### Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-20
ECLASS 15.0	27-44-02-20		

Drawings

