

CABTITE BP 7MM PA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The blanking plugs are used for the safe closing of unneeded cable passages in the sealing elements.

General ordering data

Version	Blind plug, Cabtite (cable entry system), Polyamide, white, Height: 16 mm, Width: 7 mm, Depth: 16 mm, -40 °C...120 °C, IP66
Order No.	2652350000
Type	CABTITE BP 7MM PA
GTIN (EAN)	4050118662450
Qty.	25 items

CABTITE BP 7MM PA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	16 mm	Depth (inches)	0.6299 inch
Height	16 mm	Height (inches)	0.6299 inch
Width	7 mm	Width (inches)	0.2756 inch
Length	16 mm	Length (inches)	0.6299 inch
Diameter	7 mm	Net weight	0.52 g

Temperatures

Operating temperature	-40 °C...120 °C
-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Outer cable diameter, max.	7 mm	Outer cable diameter, min.	7 mm
UL 94 flammability rating	V-0	Halogen	No
Protection degree	IP66	Basic material	Polyamide

Classifications

ETIM 8.0	EC000879	ETIM 9.0	EC000879
ETIM 10.0	EC000879	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		