

CABTITE BP 10MM PA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The blanking plugs are used for the safe closing of unneeded cable passages in the sealing elements.

General ordering data

Version	Blind plug, Cabtite (cable entry system), Polyamide, white, Height: 16 mm, Width: 10 mm, Depth: 16 mm, -40 °C...120 °C, IP66
Order No.	2652380000
Type	CABTITE BP 10MM PA
GTIN (EAN)	405011866248 1
Qty.	25 items

CABTITE BP 10MM PA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	16 mm	Depth (inches)	0.6299 inch
Height	16 mm	Height (inches)	0.6299 inch
Width	10 mm	Width (inches)	0.3937 inch
Length	16 mm	Length (inches)	0.6299 inch
Diameter	10 mm	Net weight	2.01 g

Temperatures

Operating temperature -40 °C...120 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Outer cable diameter, max.	10 mm	Outer cable diameter, min.	10 mm
UL 94 flammability rating	V-0	Halogen	No
Protection degree	IP66	Basic material	Polyamide

Classifications

ETIM 8.0	EC000879	ETIM 9.0	EC000879
ETIM 10.0	EC000879	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		