

CABTITE BP 20MM PA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

Similar to illustration

The blanking plugs are used for the safe closing of
unnneeded cable passages in the sealing elements.

General ordering data

Version	Blind plug, Cabtite (cable entry system), Polyamide, red, Height: 22 mm, Width: 20 mm, Depth: 22 mm, -60 °C...100 °C, IP66
Order No.	2652440000
Type	CABTITE BP 20MM PA
GTIN (EAN)	4050118662542
Qty.	25 items

CABTITE BP 20MM PA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	22 mm	Depth (inches)	0.8661 inch
Height	22 mm	Height (inches)	0.8661 inch
Width	20 mm	Width (inches)	0.7874 inch
Length	22 mm	Length (inches)	0.8661 inch
Diameter	20 mm	Net weight	1.1 g

Temperatures

Operating temperature -60 °C...100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Outer cable diameter, max.	20 mm	Outer cable diameter, min.	20 mm
UL 94 flammability rating	V-0	Halogen	No
Protection degree	IP66	Basic material	Polyamide

Classifications

ETIM 8.0	EC000879	ETIM 9.0	EC000879
ETIM 10.0	EC000879	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		