


**G-2L-320/10**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

2-pole fork-type phase distribution bars are used for potential distribution to other components in the control cabinet such as circuit breakers, residual current circuit breakers and other installation devices.

**General ordering data**

Version	Phase busbar (Terminals), 63, Number of poles: 18, Insulated: , 10
Order No.	<a href="#">2658130000</a>
Type	G-2L-320/10
GTIN (EAN)	4050118672398
Qty.	20 items
Delivery status	Discontinued
Available until	2024-08-30T00:00:00+02:00
Alternative product	<a href="#">G-2L-1000/10</a>

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	9.3 mm	Depth (inches)	0.3661 inch
Height	28.5 mm	Height (inches)	1.122 inch
Width	320 mm	Width (inches)	12.5984 inch
Net weight	25.75 g		

### Temperatures

Ambient temperature -5 °C...40 °C

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

### Material data

Colour grey

### Dimensions

Pitch in mm (P) 17.80 mm

### General

Number of poles 18

### Rating data


Rated cross-section 10 mm<sup>2</sup> Rated voltage 400 V  
 Nominal current 63 A

### Classifications

ETIM 8.0	EC000215	ETIM 9.0	EC000215
ETIM 10.0	EC000215	ECLASS 14.0	27-37-13-06
ECLASS 15.0	27-37-13-06		

Drawings

Drawing



## Accessories

### Feed in terminals



Our feed-in modules facilitate handling when feeding the system. For example, the bending radius of the cable can be reduced by using a feed-in module with side entry.

### General ordering data

Type	FIT 25 GN	Version
Order No.	<a href="#">2659050000</a>	Auxiliary connection (terminal), 25 mm <sup>2</sup>
GTIN (EAN)	4050118671483	
Qty.	10 ST	
Type	FIT 25 SN	Version
Order No.	<a href="#">2659060000</a>	Auxiliary connection (terminal), 25 mm <sup>2</sup>
GTIN (EAN)	4050118671476	
Qty.	30 ST	
Type	FIT 50 GN	Version
Order No.	<a href="#">2659070000</a>	Auxiliary connection (terminal), 50 mm <sup>2</sup>
GTIN (EAN)	4050118671469	
Qty.	3 ST	
Type	FIT 50 GN/F	Version
Order No.	<a href="#">2659090000</a>	Auxiliary connection (terminal), 50 mm <sup>2</sup>
GTIN (EAN)	4050118671445	
Qty.	3 ST	
Type	FIT 50 SN	Version
Order No.	<a href="#">2659080000</a>	Auxiliary connection (terminal), 50 mm <sup>2</sup>
GTIN (EAN)	4050118671452	
Qty.	3 ST	
Type	FIT 50 SN/F	Version
Order No.	<a href="#">2659100000</a>	Auxiliary connection (terminal), 50 mm <sup>2</sup>
GTIN (EAN)	4050118671438	
Qty.	3 ST	

### End caps and covers



End caps and covers ensure the required creepage distances in the system even after the bus bars have been cut to length or in the case of free-standing contacts, and guarantee finger safety in accordance with DIN EN 50274.

## Accessories

### General ordering data

Type	PROTECTION COVER G+S /5	Version
Order No.	<a href="#">2659040000</a>	Terminal cover, yellow, Height: 18.3 mm, Width: 8.1 mm, Depth: 18 mm
GTIN (EAN)	4050118671490	
Qty.	10 ST	
Type	END CAP G+S 2L/10	Version
Order No.	<a href="#">2658980000</a>	Terminal cover, grey, Height: 9.3 mm, Width: 8.2 mm, Depth: 14.5 mm
GTIN (EAN)	4050118671544	
Qty.	10 ST	