


G-3L-106/16 C**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

3-pole fork-type phase distribution bars are used for potential distribution to other components in the control cabinet such as circuit breakers, residual current circuit breakers and other installation devices.

General ordering data

Version	Phase busbar (Terminals), 80, Number of poles: 6, Insulated: , 16
Order No.	2658340000
Type	G-3L-106/16 C
GTIN (EAN)	4050118672183
Qty.	20 items
Delivery status	Discontinued
Available until	2024-08-30T00:00:00+02:00
Alternative product	G-3L-1000/16 C

Technical data

Approvals

Approvals



ROHS	Conform
------	---------

Dimensions and weights

Depth	15.4 mm	Depth (inches)	0.6063 inch
Height	31 mm	Height (inches)	1.2205 inch
Width	108 mm	Width (inches)	4.252 inch
Net weight	48 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Colour	grey
--------	------

Dimensions

Pitch in mm (P)	17.80 mm
-----------------	----------

General

Number of poles	6
-----------------	---

Rating data


Rated cross-section	16 mm ²	Rated voltage	400 V
Nominal current	80 A		

Classifications

ETIM 8.0	EC000215	ETIM 9.0	EC000215
ETIM 10.0	EC000215	ECLASS 14.0	27-37-13-06
ECLASS 15.0	27-37-13-06		

Drawings

Drawing



Accessories

Feed in terminals



Our feed-in modules facilitate handling when feeding the system. For example, the bending radius of the cable can be reduced by using a feed-in module with side entry.

General ordering data

Type	FIT 25 GN	Version
Order No.	2659050000	Auxiliary connection (terminal), 25 mm ²
GTIN (EAN)	4050118671483	
Qty.	10 ST	
Type	FIT 25 SN	Version
Order No.	2659060000	Auxiliary connection (terminal), 25 mm ²
GTIN (EAN)	4050118671476	
Qty.	30 ST	
Type	FIT 50 GN	Version
Order No.	2659070000	Auxiliary connection (terminal), 50 mm ²
GTIN (EAN)	4050118671469	
Qty.	3 ST	
Type	FIT 50 GN/F	Version
Order No.	2659090000	Auxiliary connection (terminal), 50 mm ²
GTIN (EAN)	4050118671445	
Qty.	3 ST	
Type	FIT 50 SN	Version
Order No.	2659080000	Auxiliary connection (terminal), 50 mm ²
GTIN (EAN)	4050118671452	
Qty.	3 ST	
Type	FIT 50 SN/F	Version
Order No.	2659100000	Auxiliary connection (terminal), 50 mm ²
GTIN (EAN)	4050118671438	
Qty.	3 ST	

End caps and covers



End caps and covers ensure the required creepage distances in the system even after the bus bars have been cut to length or in the case of free-standing contacts, and guarantee finger safety in accordance with DIN EN 50274.

Accessories

General ordering data

Type	PROTECTION COVER G+S /5	Version	
Order No.	2659040000	Terminal cover, yellow, Height: 18.3 mm, Width: 8.1 mm, Depth: 18	
GTIN (EAN)	4050118671490	mm	
Qty.	10 ST		
Type	END CAP G+S 3L/16	Version	
Order No.	2659600000	Terminal cover, grey, Height: 21.2 mm, Width: 8.3 mm, Depth: 16.8	
GTIN (EAN)	4050118673548	mm	
Qty.	10 ST		