

## FIT 25 GN

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



Our feed-in modules facilitate handling when feeding the system. For example, the bending radius of the cable can be reduced by using a feed-in module with side entry.

### General ordering data

Version	Auxiliary connection (terminal), 25 mm <sup>2</sup>
Order No.	<a href="#">2659050000</a>
Type	FIT 25 GN
GTIN (EAN)	4050118671483
Qty.	10 items
Delivery status	Discontinued
Available until	2025-06-01T00:00:00+02:00

## FIT 25 GN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	19.5 mm	Depth (inches)	0.7677 inch
Height	34 mm	Height (inches)	1.3386 inch
Width	13.5 mm	Width (inches)	0.5315 inch
Net weight	10 g		

### Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	08c53393-8863-492c-addc-d040b46da0d3

### Material data

Colour	grey
--------	------

### Rating data

Rated cross-section	25 mm <sup>2</sup>	Nominal current	101 A
---------------------	--------------------	-----------------	-------

### Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-08
ECLASS 15.0	27-25-03-08		