

FIT 50 GN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Our feed-in modules facilitate handling when feeding the system. For example, the bending radius of the cable can be reduced by using a feed-in module with side entry.

General ordering data

Version	Auxiliary connection (terminal), 50 mm ²
Order No.	2659070000
Type	FIT 50 GN
GTIN (EAN)	4050118671469
Qty.	3 items
Delivery status	Discontinued
Available until	2025-06-01T00:00:00+02:00

FIT 50 GN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	27 mm	Depth (inches)	1.063 inch
Height	39.7 mm	Height (inches)	1.563 inch
Width	17.8 mm	Width (inches)	0.7008 inch
Net weight	28 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	08c53393-8863-492c-addc-d040b46da0d3

Material data

Colour	grey
--------	------

General

Number of poles	1
-----------------	---

Rating data

Rated cross-section	50 mm ²	Nominal current	150 A
---------------------	--------------------	-----------------	-------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-08
ECLASS 15.0	27-25-03-08		