

## FIT 50 GN/F

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



Our feed-in modules facilitate handling when feeding the system. For example, the bending radius of the cable can be reduced by using a feed-in module with side entry.

### General ordering data

Version	Auxiliary connection (terminal), 50 mm <sup>2</sup>
Order No.	<a href="#">2659090000</a>
Type	FIT 50 GN/F
GTIN (EAN)	4050118671445
Qty.	3 items
Delivery status	Discontinued
Last order date	2024-08-30T00:00:00+02:00
Alternative product	<a href="#">FIT 50 GN</a>

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	27 mm	Depth (inches)	1.063 inch
Height	39.7 mm	Height (inches)	1.563 inch
Width	17.8 mm	Width (inches)	0.7008 inch
Net weight	30 g		

**Temperatures**

Ambient temperature	-5 °C...40 °C
---------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	08c53393-8863-492c-addc-d040b46da0d3

**Material data**

Colour	grey
--------	------

**General**

Number of poles	1
-----------------	---

**Rating data**

Rated cross-section	50 mm <sup>2</sup>	Nominal current	150 A
---------------------	--------------------	-----------------	-------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-08
ECLASS 15.0	27-25-03-08		