

CB-UVR 290/4,5 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



UV-resistant polyamide 6.6 ensures long durability of our special cable ties even with strong UV radiation. Ideal for continuous outdoor use.

General ordering data

Version	Cable ties, 4,5 x 290 mm, Polyamide 66, 220 N
Order No.	2659350000
Type	CB-UVR 290/4,5 BK
GTIN (EAN)	4050118682816
Qty.	100 items

CB-UVR 290/4,5 BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	290 mm	Height (inches)	11.4173 inch
Width	4.5 mm	Width (inches)	0.1772 inch
Net weight	1.9 g		

Temperatures

Operating temperature range	-40...85 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	105 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

UV-resistant	Yes	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	79 mm	Basic material	Polyamide 66
Tensile strength	220 N	Bundle diameter, max.	78 mm
Tensile strength (Pound-force)	49 lbf	Bundle diameter, min.	3.5 mm

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Drawings

