


## CB-HTR 365/7,5 BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Our heat-stabilised cable ties made of polyamide 6.6 are suitable for continuous use at temperatures up to +125°C.

### General ordering data

Version	Cable ties, 7.5 x 365 mm, Polyamide 66, 540 N
Order No.	<a href="#">2659420000</a>
Type	CB-HTR 365/7,5 BK
GTIN (EAN)	4050118682885
Qty.	100 items

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	1 mm	Depth (inches)	0.0394 inch
Height	365 mm	Height (inches)	14.3701 inch
Width	7.5 mm	Width (inches)	0.2953 inch
Net weight	4.21 g		

**Temperatures**

Operating temperature range	-40...125 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	125 °C		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Installation materials**

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	125 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	100 mm	Basic material	Polyamide 66
Tensile strength	540 N	Bundle diameter, max.	100 mm
Tensile strength (Pound-force)	121 lbf	Bundle diameter, min.	8 mm

**Classifications**

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

**Drawings**

