


CB-HTR 140/3,6 NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Our heat-stabilised cable ties made of polyamide 6.6 are suitable for continuous use at temperatures up to +125°C.

General ordering data

| | |
|------------|---|
| Version | Cable ties, 3.5 x 140 mm, Polyamide 66, 180 N |
| Order No. | 2659440000 |
| Type | CB-HTR 140/3,6 NC |
| GTIN (EAN) | 4050118682908 |
| Qty. | 100 items |

CB-HTR 140/3,6 NC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 1 mm | Depth (inches) | 0.0394 inch |
| Height | 140 mm | Height (inches) | 5.5118 inch |
| Width | 3.5 mm | Width (inches) | 0.1378 inch |
| Net weight | 0.6 g | | |

Temperatures

| | | | |
|----------------------------------|--------------|----------------------------------|--------|
| Operating temperature range | -40...125 °C | Continuous operating temp., min. | -40 °C |
| Continuous operating temp., max. | 125 °C | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Installation materials

| | | | |
|-----------------------------------|--------|-----------------------------------|--------------|
| UV-resistant | No | For re-opening | No |
| UL 94 flammability rating | V-2 | Operating temperature range, max. | 125 °C |
| Operating temperature range, min. | -40 °C | Halogen | No |
| Cable diameter, max. | 35 mm | Basic material | Polyamide 66 |
| Tensile strength | 180 N | Bundle diameter, max. | 32 mm |
| Tensile strength (Pound-force) | 40 lbf | Bundle diameter, min. | 2.5 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000046 | ETIM 9.0 | EC000046 |
| ETIM 10.0 | EC000046 | ECLASS 14.0 | 27-14-07-02 |
| ECLASS 15.0 | 27-14-07-02 | | |

Drawings

