


CB-VT 365/7,5 WT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Our self-extinguishing cable ties are suitable for environments with increased fire protection requirements. They comply with EN45545 and are suitable for use in rail vehicles.

General ordering data

Version	Cable ties, 7.5 x 365 mm, Polyamide 66, 540 N
Order No.	2659540000
Type	CB-VT 365/7,5 WT
GTIN (EAN)	4050118683004
Qty.	100 items

CB-VT 365/7,5 WT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	365 mm	Height (inches)	14.3701 inch
Width	7.5 mm	Width (inches)	0.2953 inch
Net weight	4.21 g		

Temperatures

Operating temperature range	-40...85 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	85 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-0	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	100 mm	Basic material	Polyamide 66
Tensile strength	540 N	Bundle diameter, max.	100 mm
Tensile strength (Pound-force)	121 lbf	Bundle diameter, min.	8 mm

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Drawings

