

**HDC XX6A01 MMSXXX-0400**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

|            |  |
|------------|--|
| Order No.  | 2659970400                             |
| Type       | <a href="#">HDC XX6A01 MMSXXX-0400</a> |
| GTIN (EAN) | 4050118673661                          |
| Qty.       | 1 items                                |

## HDC XX6A01 MMSXXX-0400

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |     |
|------------|-----|
| Net weight | 0 g |
|------------|-----|

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5 |

## General data

|                       |                    |                       |            |
|-----------------------|--------------------|-----------------------|------------|
| Number of poles       | 8                  | Cable length          | 4 m        |
| Coding                | X-coded            | Contact surface       | Au (Gold)  |
| Transmission rate     | 10 Gbps, 10 Gbit/s | Insulation resistance | ≥ 108 Ω    |
| Category              | Cat. 6A            | Nominal voltage       | 50 V       |
| Nominal current       | 0.5 A              | Plugging cycles       | ≥ 2265 100 |
| Type                  | Pin                | Pollution severity    | 2          |
| Opposite side version | Male               | Module side version   | Male       |

## Cable technical specifications

|                  |                 |        |
|------------------|-----------------|--------|
| Cable length     | 4 m             |        |
| Sheathing colour | blue            |        |
| Halogen          | No              |        |
| Insulation       | Expanded        |        |
| Sheath material  | Radox EM 104    |        |
| Outside diameter | Diameter        | 8.1 mm |
|                  | Signs           | ±      |
|                  | Tolerance       | 0.5 mm |
| Outside diameter | 8.1 mm ± 0.5 mm |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ETIM 10.0   | EC002599    | ECLASS 14.0 | 27-06-03-07 |
| ECLASS 15.0 | 27-06-03-07 |             |             |