

**KEBx HS 302620 S4B1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Klippon® EBx HS stainless steel enclosures, that the lid is fixed by Hinge and Screws, are offered as high quality and with leading performance characteristics in oil and chemistry hazardous industry. It is certified and comply with the international standards- including ATEX and IEC Ex, UL, also comply with latest CCC approval.

**General ordering data**

Version	Klippon EBx HS (Essential Box Ex - Hinge Screw), Empty enclosure, Height: 300 mm, Width: 260 mm, Depth: 200 mm, Gland plates: Bottom, Basic material: Stainless steel 1.4404 (316L), Brushed, Natural
Order No.	<a href="#">2660200130</a>
Type	KEBx HS 302620 S4B1
GTIN (EAN)	6944 1698 13924
Qty.	1 items
Local product	Only available in certain countries

**KEBx HS 302620 S4B1**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E508186

**General ordering data**

Local product	Only available in certain countries
---------------	-------------------------------------

**Dimensions and weights**

Depth	200 mm	Depth (inches)	7.874 inch
Height	300 mm	Height (inches)	11.811 inch
Width	260 mm	Width (inches)	10.2362 inch
Net weight	6400 g		

**Temperatures**

Operating temperature	-55 °C...135 °C
-----------------------	-----------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Cable glands, left**

M50	1	M32	7
M25	12	M20	16
M40	5		

**Cable glands, right**

M25	15	M40	6
M50	2	M32	8
M20	18		

**Cable glands, top/bottom**

M20	15	M40	6
M32	6	M25	12
M50	2		

**Certificate numbers enclosure**

Declaration of Conformity No. (DoC LVD)	DE PS265X 191203 000ISS01	Attestation of Conformity No. (AoC)	DE PS265X 191204 000ISS02
Certificate no. (cULus)	E508186		

## KEBx HS 302620 S4B1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### General information

Material thickness of cover	1.5 mm	Material thickness of flange	3 mm
Material thickness of enclosure	1.5 mm	Operating temperature, max.	135 °C
Operating temperature, min.	-55 °C	Lid attachment	M6 hex-head slotted screws SW10 + hinges
Standards	EN 60079-0, EN 60079-11, EN 60079-31, EN 60079-7, IEC 60079-0, IEC 60079-11, IEC 60079-31, IEC 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.3	Surface finish	Brushed
Impact resistance	7 J ATEX version, 10 J version standard	Protection degree	IP66
Basic material	Stainless steel 1.4404 (316L)	Seal material	Silicone
Torque for lid screws	2.5 Nm	Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread
Enclosure attachment	4 or 6, M6/M8 blind thread hole on backside; optionally via additional mounting feet	Flange plate mounting	M6 hexagonal head screws 10 SW
Seal material of flange plate	Silicone	Protection class (UL)	Type 3, Type 4X, Type 5
Number of lid screws	2	Gland plates	Bottom
Access opening: width	203.5 mm	Opening angle lid	115.00 °
Flange plate	Yes	Lid	Yes
Access opening: height	269 mm	Position PE bolts	Enclosure side C
Areas of use	Chemical industry, Explosive risk zone, Offshore, Oil and gas industry, Onshore, Process industry		

### horizontal assembly

WDU 10 / ZDU 10	2x15	WDU 16 / ZDU 16	2x12
WDU 2,5 / ZDU 2,5 / IDU 2,5	3x30	WDU 35 / ZDU 35	1x6
WDU 4 / ZDU 4	2x25	WDU 6 / ZDU 6	2x19

### vertical assembly

WDU 10 / ZDU 10	2x19	WDU 16 / ZDU 16	1x15
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x38	WDU 35 / ZDU 35	1x9
WDU 4 / ZDU 4	2x32	WDU 6 / ZDU 6	2x24

### Important note

Product information Exclusively available in Asia

### Classifications

ETIM 8.0	EC002503	ETIM 9.0	EC002503
ETIM 10.0	EC002503	ECLASS 14.0	27-18-05-02
ECLASS 15.0	27-18-05-02		

KEBx HS 302620 S4B1

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

[www.weidmueller.com](http://www.weidmueller.com)

