




Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Product image**





Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## **General ordering data**

Version	A-series, End bracket	
Order No.	<u>2661280000</u>	
Туре	AEB 35 SCL/1 V0	
GTIN (EAN)	4050118702163	
Qty.	20 items	





## Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Approvals			
ROHS	Conform		
Dimensions and weights	Osmorni		
Dimensions and weights			
Depth	36.5 mm	Depth (inches)	1.437 inch
Depth including DIN rail	37 mm	Height	52.6 mm
Height (inches)	2.0709 inch	Width	6 mm
Width (inches)	0.2362 inch	Net weight	5.55 g
Temperatures			
Storage temperature	-25 °C55 °C	Ambient temperature	-5 °C40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
Environmental Product Con		osimiasas sporamig tempi, maxi	.00 0
RoHS Compliance Status	Compliant without exe	emption	
REACH SVHC	No SVHC above 0.1 w	vt%	
Product Carbon Footprint	Cradle to gate 0.064 kg CO2 eq.		
Material data			
Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		
System specifications			
Mounting rail	TS 35		
Additional technical data			
Type of mounting	Snap-on	Locking	screwless
General	опар-оп	LOCKING	SCIEWIESS
General			
Mounting rail	TS 35		
Classifications			
ETIM 6.0	EC001041	ETIM 7.0	EC001041
		ETIM 7.0	
ETIM 8.0	EC001041 EC001041	ETIM 9.0 ECLASS 9.0	EC001041 27-14-11-35
ETIM 10.0 ECLASS 9.1	27-14-11-35	ECLASS 9.0 ECLASS 10.0	27-14-11-35
ECLASS 9.1 ECLASS 11.0		ECLASS 10.0 ECLASS 12.0	
	27-14-11-35 27-25-03-02		27-14-11-35
ECLASS 13.0		ECLASS 14.0	27-25-03-02
ECLASS 15.0	27-25-03-02		

Creation date 04.11.2025 08:15:37 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Accessories

#### Blank



The WAD connector marker is suitable for W-series terminals and for the WEW 35/2 and ZEW 35/2 end brackets. The markers are available as blank markers, with custom printing or standard print with lightning symbol. The WAD MultiCard markers are suitable for labelling with PrintJet CONNECT printers.For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### General ordering data

Type WAD 5 MC NE WS
Order No. 1112910000
GTIN (EAN) 4032248891689
Oty. 48 ST

Version

Group markers, Cover,  $33.3 \times 5$  mm, Pitch in mm (P): 5.00 WDU 2.5,

WEW 35/2, ZEW 35/2, white

#### With lightning flash



The WAD connector marker is suitable for W-series terminals and for the WEW 35/2 and ZEW 35/2 end brackets. The markers are available as blank markers, with custom printing or standard print with lightning symbol. The WAD MultiCard markers are suitable for labelling with PrintJet CONNECT printers.For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### General ordering data

Type WAD 5 MC B GE/SW
Order No. 1120450000
GTIN (EAN) 4032248901272
Oty 48 ST

Version

Group markers, Cover, 33.3 x 5 mm, Pitch in mm (P): 5.00 WDU 2.5,

WEW 35/2, ZEW 35/2, yellow

### **Custom printing**



The WAD connector marker is suitable for W-series terminals and for the WEW 35/2 and ZEW 35/2 end brackets. The markers are available as blank markers, with custom printing or standard print with lightning symbol. The WAD MultiCard markers are suitable for labelling with PrintJet CONNECT printers.For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## **General ordering data**

Type WAD 5 MC SDR
Order No. 1112930000
GTIN (EAN) 4032248891764

12 ST

Qty.

Version

Group markers, Cover, 33.3 x 5 mm, Pitch in mm (P): 5.00 WDU 2.5,

WEW 35/2, ZEW 35/2, To customer specification

Creation date 04.11.2025 08:15:37 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Accessories

#### Plus



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- · Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

#### **General ordering data**

800 ST

Type	DEK 5/8 PLUS MC NE WS	Version
Order No.	1046350000	Dekafix
GTIN (EAN)	4032248782055	Weidm

/ersion

Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00

Weidmueller, white

#### **Blank**

Qty.



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text. WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### **General ordering data**

Туре	WS 10/8 PLUS MC NE WS	Version
Order No.	<u>1905950000</u>	WS, Terminal marker, 10 x 8 mm, Pitch in mm (P): 8.00 Weidmueller,
GTIN (EAN)	4032248528103	white
Qty.	420 ST	
Туре	DEK 5/6 MC NE WS	Version
Type Order No.	DEK 5/6 MC NE WS 1609820000	Version  Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
	'	

Creation date 04.11.2025 08:15:37 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Accessories

#### Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadiummolybdenum steel, gun-metal finish.

#### General ordering data

Type SDIS SLIM 0.6X3.5X100 Order No. 2749610000 GTIN (EAN) 4050118896350 Qty.

Version Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm

#### WS 8/6



#### WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wearresistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- · Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- · Large label field for optimal legibility
- · High flexibility thanks to manufacturer independence

### General ordering data

Type	WS 8/6 MM WS	Version
Order No.	2007160000	WS, T
GTIN (EAN)	4050118391879	
Qty.	600 ST	

Terminal marker, 8 x 6 mm, Weidmueller, white



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Accessories

## **ZGB** pivotable group tag holder



The ZGB 15 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 15.

The ZGB 30 is a hinged group tag carrier. The tag carrier can hold the dekafix 5, WS 12/5 terminal markers or the inlay tag ESO 7.

Inlay tags and protective strips can be found under "Accessories".

### **General ordering data**

Type ZGB 30 Order No. <u>1611930000</u> GTIN (EAN) 4008190002251 Oty. 20 ST Version

Terminal markers, Terminal marker, 32 x 7 mm, Pitch in mm (P): 5.00

Weidmueller, white