Data sheet

SAIEND 1/4 M8G 3P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Passive M12 distributors are available in all conceivable forms and configurations. Furthermore, a number of special versions, e.g. SAI distributors for EX zones or the ergonomic M8, are available only from Weidmüller. These innovative products are backed up by numerous proprietary rights.

General ordering data

Version	M8, LED: , LED initiator: , Wiring type:
Order No.	2662450000
Type	SAIEND 1/4 M8G 3P
GTIN (EAN)	4050118677379
Qty.	1 items

SAIEND 1/4 M8G 3P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform

Dimensions and weights

Net weight	4.4 g

Temperatures

Operating temperature	-25 - 85°C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	1c533b66-fcff-4da5-b89f-fd55fbf5cb55

General technical data

Protection degree	IP67	Number of poles	3
Connection thread	M8	Pollution severity	3
Plugging cycles	≥ 100		

Technical data cable

Number of poles	3

Classifications

ETIM 8.0	EC000448	ETIM 9.0	EC000448
ETIM 10.0	EC000448	ECLASS 14.0	19-07-04-03
ECLASS 15.0	19-07-04-03		

SAIEND 1/4 M8G 3P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings





