

IE-PIC-M12X-P-22/26

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Machined precision crimp contacts for M12X

General ordering data

Version	Contact, without, Pin
Order No.	2664880000
Type	IE-PIC-M12X-P-22/26
GTIN (EAN)	4050118765342
Qty.	100 items

IE-PIC-M12X-P-22/26

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	0.05 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Technical data customisable plug-in connectors

Number of poles	1	Coding	X-coded
Connection cross-section	AWG 22 - AWG 26	LED	No
Type of connection	Crimp connection	Contact material	Copper alloy, Gold-plated
Conductor cross-section, max.	0.14 mm ²	Conductor cross-section, min.	0.34 mm ²
Nominal current	1 A	Protection degree	IP00
Shield connection	No	Threaded ring material	None

General Info

Number of poles	1	Connection 1	M12 Contact
Connection 2	Crimp	Connection thread	without
Contact material	Copper alloy, Gold-plated	Protection degree	IP00

Electrical properties

Contact resistance	≤ 10 mΩ
--------------------	---------

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

