

STARTERKIT-UC20-WL2000-IOT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Order No.	2666060000
Type	STARTERKIT-UC20-WL2000-IOT
GTIN (EAN)	4050118681550
Qty.	1 items

STARTERKIT-UC20-WL2000-IOT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	455 mm	Depth (inches)	17.9134 inch
Height	320 mm	Height (inches)	12.5984 inch
Width	255 mm	Width (inches)	10.0394 inch
Mounting dimension - height	320 mm	Net weight	800 g

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	8eb7beda-d24b-434b-95c4-ddc050faf33c

General data

Mounting rail	TS 35
---------------	-------

Power supply

Supply voltage for outputs	24 V DC +20 %/ -15 %	Supply voltage system and inputs	230 V AC
----------------------------	----------------------	----------------------------------	----------

System data

Interface	2 x Ethernet 10/100/1000 MBit/s (RJ45), 1x Micro USB	max. number of modules	0
Configuration interface	Micro USB 2.0, MicroSD CARD	Program data memory expansion possible	Yes
Engineering tool	u-create web	Programming environment	web-based
Memory (Flash)	4 GB	Real-time clock	Capacity buffered (max. 5 days)
Field bus protocol	TCP/IP		

Classifications

ETIM 8.0	EC000236	ETIM 9.0	EC000236
ETIM 10.0	EC000236	ECLASS 14.0	27-24-22-07
ECLASS 15.0	27-24-22-07		