

STARTERKIT-UC20-SL2000-AC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Order No.	2666070000
Type	STARTERKIT-UC20-SL2000-AC
GTIN (EAN)	4050118681543
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2024-03-31T00:00:00+01:00
Alternative product	STARTERKIT-UC20-WL2000-AC

STARTERKIT-UC20-SL2000-AC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	455 mm	Depth (inches)	17.9134 inch
Height	320 mm	Height (inches)	12.5984 inch
Width	255 mm	Width (inches)	10.0394 inch
Net weight	800 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	8eb7beda-d24b-434b-95c4-ddc050faf33c

Connection data

Wire cross-section, finely stranded, max. (AWG)	AWG 26	Wire cross-section, finely stranded, min. (AWG)	AWG 16
Wire cross-section, solid, max. (AWG)	AWG 26	Wire cross-section, solid, min. (AWG)	AWG 16
Type of connection	PUSH IN	Wire cross-section, solid, max.	1.5 mm ²
Wire connection cross section, finely stranded, max.	1.5 mm ²	Wire connection cross section, finely stranded, min.	0.14 mm ²

Power supply

Supply voltage for outputs	230 V AC
----------------------------	----------

System data

max. number of modules	0	Configuration interface	Micro USB 2.0
Program data memory expansion possible	Yes	User data memory size	4 GB
Connection type	PUSH IN	Programming environment	CoDeSys based
Type of program data memory	DDR4	Memory (Flash)	32 GB via microSD, 4 GB

Classifications

ETIM 8.0	EC000236	ETIM 9.0	EC000236
ETIM 10.0	EC000236	ECLASS 14.0	27-24-22-07
ECLASS 15.0	27-24-22-07		