

STARTERKIT-UC20-WL2000-AC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Order No.	2666080000
Type	STARTERKIT-UC20-WL2000-AC
GTIN (EAN)	4050118681536
Qty.	1 items

STARTERKIT-UC20-WL2000-AC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	455 mm	Depth (inches)	17.9134 inch
Height	320 mm	Height (inches)	12.5984 inch
Width	255 mm	Width (inches)	10.0394 inch
Net weight	800 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cI
REACH SVHC	Lead 7439-92-1
SCIP	8eb7beda-d24b-434b-95c4-ddc050faf33c

Connection data

Type of connection	PUSH IN
--------------------	---------

Power supply

Supply voltage for outputs	24 V DC +20 %/ -15 %	Supply voltage system and inputs	24 V DC +20 %/ -15 %
----------------------------	----------------------	----------------------------------	----------------------

System data

Configuration interface	Micro USB 2.0	Processor	Dual Core ARM Cortex A9, 624 MHz, 512 Mbyte RAM
Connection type	PUSH IN	Programming environment	web-based
Memory (Flash)	8 GB	Real-time clock	Battery buffered
Field bus protocol	EtherCAT, Modbus/TCP, PROFINET, EtherNet/IP		

Classifications

ETIM 8.0	EC000236	ETIM 9.0	EC000236
ETIM 10.0	EC000236	ECLASS 14.0	27-24-22-07
ECLASS 15.0	27-24-22-07		