


**HDC MBUS 2 F MCLIP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

**General ordering data**

Version	Data module, 0 V, Number of poles: 0, Crimp connection, Female, Required plug-in slots: 1
Order No.	<a href="#">2667180000</a>
Type	HDC MBUS 2 F MCLIP
GTIN (EAN)	4050118803860
Qty.	1 items

## HDC MBUS 2 F MCLIP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Height	41.2 mm	Height (inches)	1.622 inch
Width	14.5 mm	Width (inches)	0.5709 inch
Net weight	2.2 g		

### Temperatures

Limit temperature -40 °C ... 125 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

### General data

Number of poles	0	UL 94 flammability rating	V-0
Insulation resistance	1012 Ω	Plugging cycles	≥ 500
Type	Female	Surge voltage category	III
Pollution severity	3	Basic material	Polycarbonate, glass fibre reinforced
Series	ModuPlug	Rated voltage (DIN EN 61984)	0 V
Required plug-in slots	1		

### PE connection data

Connection type PE Screw connection via module frame

### Version

Type of connection Crimp connection

### Classifications

ETIM 8.0	EC002641	ETIM 9.0	EC002641
ETIM 10.0	EC002641	ECLASS 14.0	27-44-03-12
ECLASS 15.0	27-44-03-12		

**HDC MBUS 2 F MCLIP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

