

**HDC MHP70 F 10**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	Female, silver, 10 - 10 mm <sup>2</sup>
Order No.	<a href="#">2668200000</a>
Type	HDC MHP70 F 10
GTIN (EAN)	4050118803006
Qty.	10 items

**HDC MHP70 F 10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Net weight 7.2 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant with exemption  
 RoHS Exemption (if applicable/known) 6c  
 REACH SVHC Lead 7439-92-1  
 SCIP 6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

**General data**

Contact diameter, male Ø	6 mm	Stripping length, rated connection	16 mm
Type of connection	Crimp connection	Version insert	MHP
Conductor cross-section, max.	10 mm <sup>2</sup>	Conductor cross-section, min.	10 mm <sup>2</sup>
Surface finish	silver	Plugging cycles	≥ 500
Type	Female	Basic material	Copper alloy
Series	ModuPlug	Production methods	turned
Cross-section for connected wire	10 - 10 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

**HDC MHP70 F 10**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

