

HDC MHP70 M 25

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Version	Male, silver, 25 - 25 mm ²
Order No.	2668370000
Type	HDC MHP70 M 25
GTIN (EAN)	4050118803013
Qty.	10 items

HDC MHP70 M 25

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 10.8 g

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
RoHS Exemption (if applicable/known) 6c
REACH SVHC Lead 7439-92-1
SCIP 6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

General data

Contact diameter, male Ø	6 mm	Stripping length, rated connection	16 mm
Type of connection	Crimp connection	Version insert	MHP
Conductor cross-section, max.	25 mm ²	Conductor cross-section, min.	25 mm ²
Surface finish	silver	Plugging cycles	≥ 500
Type	Male	Basic material	Copper alloy
Series	ModuPlug	Production methods	turned
Cross-section for connected wire	25 - 25 mm ²		

Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

HDC MHP70 M 25

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

