

CRIMPER 4U Z GER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, 0.5mm ² , 4mm ² , Trapezoidal crimp
Order No.	2676320000
Type	CRIMPER 4U Z GER
GTIN (EAN)	4050118742213
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-02-28T00:00:00+01:00

CRIMPER 4U Z GER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Height	78 mm	Height (inches)	3.0709 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	16.92 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Description of contact

Type of contact	Wire-end ferrules with/without plastic collars	Crimping range, max.	4 mm ²
Crimping range, min.	0.5 mm ²		

tool data crimping

Wire end ferrules cross-section, max.	4 mm ²	Crimping type/profile	Trapezoidal crimp
---------------------------------------	-------------------	-----------------------	-------------------

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		