



The Weidmüller connecting module is helpful whenever you have to repair or want to extend a broken installation cable without cable reserve in confined spaces.

General ordering data

Version	Connecting module, T-piece, IP68 (50 m / 24 h)
Order No.	2685590000
Type	IE-CCTM-3P-8.5
GTIN (EAN)	4050118695342
Qty.	1 items

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E486077

Dimensions and weights

Net weight	35 g
------------	------

Temperatures

Storage temperature	Operating temperature	-40 °C...105 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

General Info

Number of poles	3	Colour	black
Housing main material	Nylon, Glass fibre, UL recognized	Contact material	Brass, nickel plated
Contact surface	Nickel-plated CuZn	Wire connection cross section, finely stranded, min.	0.75 mm ²
Wire connection cross section, finely stranded, max.	3.5 mm ²	Conductor connection cross-section, flexible	0.75...3.5 mm ²
Protection degree	IP68 (50 m / 24 h)		

Electrical properties

Nominal voltage	600 V	Rated current	20 A
-----------------	-------	---------------	------

General standards


Certificate No. (cURus)	E486077
-------------------------	---------

Classifications

ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 14.0	27-40-02-12
ECLASS 15.0	27-40-02-12		

Drawings

Dimensioned drawing



Installation cut-out

