

HDC MHP70 M 25 P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

| | |
|------------|---------------------------------------|
| Version | Male, silver, 25 - 25 mm ² |
| Order No. | 2691260000 |
| Type | HDC MHP70 M 25 P |
| GTIN (EAN) | 4050118803037 |
| Qty. | 10 items |

HDC MHP70 M 25 P

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 9.68 g

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 6eabd5ae-2d6b-409e-8bdf-87c27ee10e40 |

General data

| | | | |
|----------------------------------|-------------------------|------------------------------------|--------------------|
| Contact diameter, male Ø | 6 mm | Stripping length, rated connection | 16 mm |
| Type of connection | Crimp connection | Version insert | MHP |
| Conductor cross-section, max. | 25 mm ² | Conductor cross-section, min. | 25 mm ² |
| Surface finish | silver | Plugging cycles | ≥ 500 |
| Type | Male | Basic material | Copper alloy |
| Series | ModuPlug | Production methods | turned |
| Cross-section for connected wire | 25 - 25 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000796 | ETIM 9.0 | EC000796 |
| ETIM 10.0 | EC000796 | ECLASS 14.0 | 27-44-02-04 |
| ECLASS 15.0 | 27-44-02-04 | | |

HDC MHP70 M 25 P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

