

IE-USB-A-A-1.0M-ML

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	USB cable, USB A, with mechanical locking, USB A, with mechanical locking, PVC, 1 m
Order No.	2695980010
Type	IE-USB-A-A-1.0M-ML
GTIN (EAN)	4050118702828
Qty.	1 items

IE-USB-A-A-1.0M-ML

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Length	1 m	Length (inches)	39.3701 inch
Net weight	42 g		

Temperatures

Storage temperature	Operating temperature	0 °C...80 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical specifications for cable

Sheathing colour black

General technical data

Contact surface Gold over nickel

Cable structure

Sheath diameter	4.5 mm	Sheathing colour	black
Cross-section	2*AWG28 + 2*AWG24	Sheath diameter, max.	4.7 mm
Sheath diameter, min.	4.3 mm	Material sheath	PVC

Plug, left

Plug left USB A, IP20, male contact, straight, plug, with mechanical locking, Plastic, shielded

Plug, right

Plug right USB A, IP20, male contact, straight, plug, with mechanical locking, Plastic, shielded

Classifications

ETIM 8.0	EC001408	ETIM 9.0	EC001408
ETIM 10.0	EC001408	ECLASS 14.0	27-06-01-06
ECLASS 15.0	27-06-01-06		


IE-USB-A-A-1.0M-ML

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensional drawing



Product benefits

