

IE-USB-A-A-1.8M-ML

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	USB cable, USB A, with mechanical locking, USB A, with mechanical locking, PVC, 1.8 m
Order No.	2695980018
Type	IE-USB-A-A-1.8M-ML
GTIN (EAN)	4050118702835
Qty.	1 items

IE-USB-A-A-1.8M-ML

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Length	1.8 m	Length (inches)	70.8661 inch
Net weight	70 g		

Temperatures

Storage temperature	Operating temperature	0 °C...80
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical specifications for cable

Sheathing colour	black
------------------	-------

General technical data

Contact surface	Gold over nickel
-----------------	------------------

Cable structure

Sheath diameter	4.5 mm	Sheathing colour	black
Cross-section	2*AWG28 + 2*AWG24	Sheath diameter, max.	4.7 mm
Sheath diameter, min.	4.3 mm	Material sheath	PVC

Plug, left

Plug left	USB A, IP20, male contact, straight, plug, with mechanical locking, Plastic, shielded
-----------	---------------------------------------------------------------------------------------

Plug, right

Plug right	USB A, IP20, male contact, straight, plug, with mechanical locking, Plastic, shielded
------------	---------------------------------------------------------------------------------------

Classifications

ETIM 8.0	EC001408	ETIM 9.0	EC001408
ETIM 10.0	EC001408	ECLASS 14.0	27-06-01-06
ECLASS 15.0	27-06-01-06		


IE-USB-A-A-1.8M-ML

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensional drawing



Product benefits

